

128mm Dia x 288mm FL Alum. Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock **#90-970** [CONTACT US](#)



1



€469,00

ADD TO CART

Qty 1-10

€469,00

Qty 11+

€411,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: BOROFLOAT®

Coating:
Protected Aluminum (400-700nm)

Coating Specification:
Ravg >85% @400 - 700nm

Coating Type: Metal
Center Hole Diameter (mm): 31.0
Height (mm): 67.7
Inner Diameter (mm): 121
Outer Diameter (mm): 128.00 +0.0/-0.5
Type: Specialty Mirror
Wavelength Range (nm): 400 - 700
Distance to Focal Point f₁ (mm) : 17.8
Distance to Focal Point f₂ (mm): 294

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
