

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 12mm Diameter X -24 FL, NIR II Coated, Plano-Concave Lens



Stock #67-994 ☐ In Stock
[Other Coating Options](#)

1 €42,00

ADD TO CART

Qty 1-9
€42,00
Qty 10+
€37,75
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):

-24.00
Substrate: N-BK7
f#: 2.00
Coating: NIR II (750-1550nm)
Type: Plano-Concave Lens
Wavelength Range (nm): 750 - 1550
Back Focal Length BFL (mm): -26.32
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 11.00
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Edge Thickness ET (mm): 4.79
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Radius R₁ (mm): -12.40
Surface Quality: 40-20
Damage Threshold, Reference: 8 J/cm² @ 1064nm, 10ns
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant