

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

12mm FL Ultra High Resolution Fixed Focal Length Lenses



#68-684



Stock #68-683 3-4 DAYS

[Similar Products](#)



1



€1.590,00

ADD TO CART

Qty 1+

€1.590,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
58.4

Iris Option:
Variable

Length (mm):
52.50

Horizontal Field of View, 1/2" Sensor: 58.4mm - 28.9°
Filter Thread: M25.5 x0.50
Maximum Diameter (mm): 33.0
Weight (g): 105.00
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 12.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/11
Maximum Distortion (%): <0.12%
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)