


12" Length, Dovetail Optical Rail



12" Length, Dovetail Optical Rail, #54-401



Stock **#54-401** 3-4 DAYS

- 1 +

€172,00

ADD TO CART

Qty 1-4

€172,00

Qty 5+

€163,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive: Manual
Type: Universal (Metric & English)
Travel (mm): 304.8
Travel (inches): 12
Length (inches): 12
Length (mm): 304.80
Construction: Black Anodized Aluminum
Mounting Threads: C'bore Holes and Slots only for ¼" (or M6) S.H.C.S
Note: Rail

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant

