

1300mW, 450nm Laser ZQ1, 45°



Stock #19-439 3-4 DAYS

- 1 + **€4.208,00**

ADD TO CART

Qty 1-9
€4.208,00
Qty 10+
€3.786,75
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
-10 to +50

Output Power (mW):

1300
Dimensions (inches): 6.26 x 2.57 x 2.03 (L x W x H)
Wavelength (nm): 450.00
Weight (g): 690
Working Distance (mm): above 3.3ft (1m)
Laser Class - IEC: 3B
Storage Temperature (°C): -40 to +85
Modulation Frequency (kHz): 200
Style: Homogeneous Line
Output Type: Free Space
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Blue
Connector: 5 Pins, M12
Fan Angle (°): 45.00
Focus Range: 100mm up to 10,000mm
Input Voltage (V): 12 - 24
Diameter of Laser Head (inches): 0.79

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View