

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

8mm Max. Aperture, Stainless Steel Iris Diaphragm



Stock #62-650 3-4 DAYS

-

1

+

 €70,00

ADD TO CART

Qty 1-4
€70,00
Qty 5+
€61,70
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
0.8

Maximum Aperture (mm):
8.0

Outer Diameter (mm):

14.8
Construction: Blackened Brass Housing, Stainless Steel Leaves
Lever Diameter (mm): 1.50
Lever Length (mm): 7.00
Number of Leaves: 8.00
Thickness (mm): 4.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)