

TECHSPEC® 14mm Protected Silver Coated, Amici Roof Prism



Amici Roof Prisms

Stock #12-639 ☒ In Stock

1 **€125,00**

ADD TO CART

Qty 1-5

€125,00

Qty 6+

€106,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
13.00

Coating:
Silver with protective overcoat

Substrate: ☐
N-BK7

Surface Quality: 60-40
Type: Amici Roof Prism
Dimensional Tolerance (mm): +0/-0.1
Angle Tolerance (arcmin): ±5
Resolution (arcsec): 6.00
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Note: Black Overpaint is 30-60µm Thick
Coating Specification: Reflective Surfaces: R _{abs} > 97% FROM400 - 2500nm @ 0° AOI R _{avg} > 98% FROM400 - 2500nm @ 0° AOI
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/2
Coating Type: Metal
Damage Threshold, By Design: ☐ 0.5 J/cm ² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View