

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 15 X 15mm Protected Gold, λ/4 Mirror



Stock #45-727 3-4 DAYS

1 €70,00

ADD TO CART

Qty 1-5

€70,00

Qty 6+

€56,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V): λ/4

Substrate:  BOROFLOAT®

Back Surface: Commercial Polish

Surface Quality: 60-40
Dimensions (mm): 15.0 x 15.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) : 85
Edges: Fine Ground
Thickness (mm): 2.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Length (mm): 15.00
Width (mm): 15.00
Damage Threshold, Reference:  0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant