

TECHSPEC® 150 x 150mm, Enhanced Aluminum, 4-6λ Mirror



Stock **#19-350** 3-4 DAYS

- 1 + **€86,50**

ADD TO CART

Qty 1-5
€86,50

Qty 6+
€67,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

150.00 x 150.00 +0.00/-0.25
Coating Specification: R _{avg} ≥95% @450 - 650nm @45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 135.00 x 135.00
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00 (nominal)
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Length (mm): 150.00
Width (mm): 150.00
Damage Threshold, By Design: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant