

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #15-180 3-4 DAYS



1



€866,00

ADD TO CART

Qty 1-4

€866,00

Qty 5+

€779,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
152.20

Maximum Diameter (mm):
87

Scan Angle (°):

±22.62
Scan Field (mm): 86.0 x 86.0
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 171.2
Wavelength Range (nm): 1064
Range Distance (mm): 189.5
Focus Size Diameter, 1/e² (μm): 26
Input Beam Diameter, 1/e² (mm): 12
Maximum Length (mm): 54.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View