

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 15.0mm Dia. X 22.5mm FL Uncoated, Plano-Convex Lens



Stock #32-004 ☐ In Stock  
[Other Coating Options](#)

1  €30,00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €30,00                        |
| Qty 10+                       |
| €27,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                                     |
|---------------------------------------------------------------------|
| 22.50 @ 587.6nm                                                     |
| <b>Back Focal Length BFL (mm):</b><br>20.50                         |
| <b>Coating:</b><br>Uncoated                                         |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">N-SF5</a> |
| <b>Surface Quality:</b><br>40-20                                    |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ                               |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4                         |
| <b>Focal Length Tolerance (%):</b><br>±1                            |
| <b>Centering (arcmin):</b><br><1                                    |
| <b>Center Thickness CT (mm):</b><br>3.35 ±0.10                      |
| <b>Edge Thickness ET (mm):</b><br>1.36                              |
| <b>Radius R<sub>1</sub> (mm):</b><br>15.12                          |
| <b>Clear Aperture CA (mm):</b><br>14                                |
| <b>f/#:</b><br>1.5                                                  |
| <b>Numerical Aperture NA:</b><br>0.33                               |
| <b>Type:</b><br>Plano-Convex Lens                                   |
| <b>Bevel:</b><br>Protective bevel as needed                         |
| <b>Wavelength Range (nm):</b><br>380 - 2500                         |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |