

152.4mm Clear Aperture 45R/55T, Infrared Pellicle Beamsplitter



Infrared (IR) Pellicle Beamsplitters

Stock #19-285 3-4 DAYS

- 1 + **€1.014,00**

ADD TO CART

Qty 1-10
€1.014,00
Qty 11+
€861,90
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads	
Clear Aperture CA (mm): 152.4	
Coating: Dielectric	
Coating Specification: 45/55 @ 3000 - 5000nm	

Construction: Pellicle
Diameter (mm): 165.10
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 9.53
Reflection/Transmission Ratio (R/T): 45/55
Substrate:  Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Wavelength Range (nm): 3000 - 5000
Mounting Threads: 6-32
Thickness (μm): 2 +0.3/-0.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View