

TECHSPEC® 15mm Dia., 0.66 Numerical Aperture Uncoated, Aspheric Lens



Stock **#47-725** 3-4 DAYS

[Other Coating Options](#)



1



€225,00

ADD TO CART

Qty 1-5

€225,00

Qty 6+

€180,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.1

Effective Focal Length EFL (mm):
11.25 @ 587.6nm

Numerical Aperture NA:

0.66
Back Focal Length BFL (mm): 6.85
Substrate: ☐ L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: Uncoated
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 13.5
Edge Thickness ET (mm): 1.94
Center Thickness CT (mm): 7.00 ±0.1
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 330 - 2400
Conjugate Distance: Infinite
Power (diopters): 88.89

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View