

15mm Dia. x 15mm EFL Arton Plastic Asphere, Coated



Stock #90-324 CLEARANCE 3-4 DAYS

- 1 + **€30,00**

ADD TO CART

Qty 1+

€30,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
15.00

Effective Focal Length EFL (mm):
15.00 ±0.2

Numerical Aperture NA:
0.40

Back Focal Length BFL (mm):
12.79

Substrate: ☐
Arton Plastic

Coating: BBAR (650-850nm)
Coating Specification: R _{abs} <1.0% @ 650 - 850nm
Clear Aperture CA (mm): 12.00
Edge Thickness ET (mm): 3.9
f/#: 1.25
Bevel: Protective bevel as needed
Flange Distance (mm): 12.79
Type: Aspheric Lens
Wavelength Range (nm): 650 - 850
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View