

165mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-181 3-4 DAYS

⊖ 1 ⊕ **€866,00**

ADD TO CART

Qty 1-4
€866,00
Qty 5+
€779,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
165.10

Maximum Diameter (mm):
109

Scan Angle (°):

±28.50
Scan Field (mm): 116.2 x 116.2
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 188.1
Wavelength Range (nm): 1064
Range Distance (mm): 219.1
Focus Size Diameter, 1/e² (μm): 26
Input Beam Diameter, 1/e² (mm): 12
Maximum Length (mm): 54.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View