

165mm FL, 532nm Edmund Optics® F-Theta Lens



Stock #15-186 3-4 DAYS

⊖ 1 ⊕ **€917,00**

ADD TO CART

Qty 1-4
€917,00

Qty 5+
€825,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
532

Focal Length FL (mm):
165.00

Maximum Diameter (mm):
106

Scan Angle (°):

±25.00
Scan Field (mm): 101.8 x 101.8
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 193.5
Wavelength Range (nm): 532
Range Distance (mm): 228.0
Focus Size Diameter, 1/e² (μm): 13
Input Beam Diameter, 1/e² (mm): 16
Maximum Length (mm): 52.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View