

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Richardson Gratings™ 1800 Grooves, 12.7 X 12.7mm, 250-900nm, Plane Holographic Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Reflective Holographic Diffraction Gratings



Stock #15-751 ☐ In Stock



€135,00

ADD TO CART

Qty 1+

€135,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1800

Wavelength Range (nm):

250 - 900
Blaze Wavelength (nm): 450
Dimensions (mm): 12.7 x 12.7 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Holographic Grating
Length (mm): 12.70
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 12.70
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S, P and Average
Master Reference: 320H
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View