

## 12mm Max. Aperture, Iris Diaphragm



Stock #30-263 3-4 DAYS

⊖ 1 ⊕ **€46,00**

ADD TO CART

|         |
|---------|
| Qty 1-4 |
| €46,00  |

|        |
|--------|
| Qty 5+ |
| €40,60 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Get Product Downloads

|                                |
|--------------------------------|
| Type:<br>Unmounted             |
| Minimum Aperture (mm):<br>0.80 |
| Maximum Aperture (mm):<br>12.0 |
| Outer Diameter (mm):           |

|                                                                   |
|-------------------------------------------------------------------|
| 19.8                                                              |
| <b>Construction:</b><br>Brass Housing, Blue Tempered Steel Leaves |
| <b>Lever Diameter (mm):</b><br>3.00                               |
| <b>Lever Length (mm):</b><br>11.50                                |
| <b>Number of Leaves:</b><br>10.00                                 |
| <b>Thickness (mm):</b><br>5.00                                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Contains SVHC(s)</a>      |