

TECHSPEC® 1" Dia, 1" FL Uncoated, Spherical Mirror



Stock **#43-335** ☐ In Stock

-

1

+

€98,00

ADD TO CART

Qty 1-9
€98,00
Qty 10+
€83,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐
BOROFLOAT®

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy: λ/4
Diameter (inches): 1.0
Diameter (mm): 25.40 +0/-0.3
Diameter Tolerance (inches): +0/-0.01
Effective Focal Length EFL (inches): 1.00
Effective Focal Length EFL (mm): 25.40
Radius of Curvature (mm): 50.80
Aperture (f/#): f/1
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Edge Thickness ET (inches): 0.25
Edge Thickness ET (mm): 6.35
Edge Thickness Tolerance (%): +0.0/-15
Type: Spherical Mirror

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View