

# 1" x 1" (2500 lp/inch), Ronchi Ruling



Stock **#56-602** 3-4 DAYS

- 1 + **€294,00**

ADD TO CART

|         |
|---------|
| Qty 1-4 |
| €294,00 |

|         |
|---------|
| Qty 5+  |
| €279,80 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

**Coating:**  
Vacuum Deposited Chrome, OD >3.0

**Dimensional Tolerance (inches):**  
±0.02

**Substrate:**  
Float Glass

**Optical Density OD (Average):**

|                                                       |
|-------------------------------------------------------|
| 3.00                                                  |
| <b>Dimensions (inches):</b><br>1 x 1                  |
| <b>Surface Quality:</b><br>60-40                      |
| <b>Thickness (mm):</b><br>1.50                        |
| <b>Type:</b><br>English                               |
| <b>Parallelism (arcmin):</b><br>±60                   |
| <b>Dimensional Tolerance (mm):</b><br>± 0.02          |
| <b>Frequency (lp/inch):</b><br>2500.00                |
| <b>Line to Line Parallelism (arcsec):</b><br>≤2       |
| <b>Parallelism of Pattern to Substrate (°):</b><br>±1 |
| <b>Surface Flatness (P-V):</b><br>1λ                  |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 209:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |