

1X 120mm WD, In-Line Illumination Telecentric Lens



Stock #59-741 3-4 DAYS

- 1 + **€1.545,00**

ADD TO CART

Qty 1+
€1.545,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
137.00

Ferrule Diameter (inches):
0.312

Horizontal Field of View, 1/2" Sensor:
6.4mm

Horizontal Field of View, 2/3" Sensor:
8.8mm

Maximum Diameter (mm):
29.5

Horizontal Field of View @ Max Sensor Format: 8.8mm
Type: Telecentric Lens
Primary Magnification PMAG: 1X
Maximum Sensor Format: 2/3"
Working Distance (mm): 120.00
Mount: C-Mount
Style: In-Line Illumination
Aperture (f#): f/16.6
Distortion (%): ≤0.1
Compatible Light Guide/Source: 1/4" (0.312")
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View