

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #59-546 3-4 DAYS

1 €264,00

ADD TO CART

Qty 1-4

€264,00

Qty 5+

€251,80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
Vacuum Deposited Chrome

Dimensional Tolerance (inches):
±0.100

Frequency (lp/mm):
20.00

Substrate:

Opal Glass
Length (mm): 25.40
Optical Density OD (Average): >3.0
Pattern Size (mm): 12.7 x 25.4
Surface Quality: 40-20
Thickness (mm): 1.52 ±0.100
Width (mm): 76.20
Note: Pattern Location is Centered
NIST Certification: No
Line Width Tolerance (µm): ±0.001

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant