

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT



Stock #39-865 3-4 DAYS



1



€132,00

ADD TO CART

Qty 1-5

€132,00

Qty 6+

€105,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate:
[ZERODUR[®]](#)

Back Surface:
Commercial Polish

Surface Quality: 20-10
Dimensions (mm): 20.0 x 20.0 +0.00/-0.20
Coating Specification: R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 3.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 20.00
Width (mm): 20.00
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference:  0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant