

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

204 X 254mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #41-321 3-4 DAYS



1



€149,00

ADD TO CART

Qty 1-5

€149,00

Qty 6+

€119,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm): 204.0 x254.0 ±0.76
Coating Specification: R_{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 1.60
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 254.00
Width (mm): 204.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
