

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #15-533 3-4 DAYS

[Other Coating Options](#)



1



€39,00

ADD TO CART

Qty 1-10

€39,00

Qty 11+

€35,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
20.40 +0.1/-0.3

Effective Focal Length EFL (mm):
25.00

Numerical Aperture NA:
0.40

Substrate: Float Glass
Focal Length Tolerance (%) : ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin) : ≤30
Surface Quality: 80-50 (typical)
Center Thickness CT (mm) : 5.30 ±0.2
f/#: 1.23
Bevel: Protective bevel as needed
Radius R₂ (mm) : Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm) : 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant