

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

208mm Max. Aperture, Iris Diapnragm



Stock #70-894 3-4 DAYS

- 1 + €750,00

ADD TO CART

Qty 1-4

€750,00

Qty 5+

€659,70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
11.0

Maximum Aperture (mm):
158.0

Outer Diameter (mm):

208.0
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 20.50
Number of Leaves: 20.00
Thickness (mm): 16.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)