

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 20mm, Al & AR Coated, Fused Silica, Right Angle Prism



TECHSPEC UV Fused Silica Right Angle Prisms

Stock #47-795 3-4 DAYS



1



€126,00

ADD TO CART

Qty 1-5

€126,00

Qty 6+

€101,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
MgF₂ & Aluminized

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Surface Quality:
60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.10 Legs
Angle Tolerance (arcmin): ±5
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 28.30
Length of Legs (mm): 20.00
Pyramid Tolerance (arcmin): ±5
Image Orientation: Left-Handed
Coating Specification: Hypotenuse: R _{avg} >85% @ 400 - 700nm Legs: R _{avg} ≤1.75% @ 400 - 700 nm
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 700
Surface Flatness (P-V): λ/2
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm ² @ 532nm & 1064nm, 10ns Legs: 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant