

Stock #13-029 3-4 DAYS

€03

1

€93,00

ADD TO CART

€83,00

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

CC BY-NC-SA



Cut-On Wavelength (nm): 530.00
Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG530
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 600.00
Spectral Transmittance t_p (%): 93.00
Stopband Limit λ_s(nm): 460.00
Surface Quality: 80-50
Transformation Temperature (°C): 506.00
Type: Longpass Filter
Wavelength: VIS
Reflection Factor P_d: 0.92
Substrate Thickness (mm): 3.00 ±0.2
Thread Type: C-Mount
Total Length (mm): 20.3
Mount Diameter (mm): 30.0
Filter Included: #46-059
Mount Included: #56-353

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View