

230V, Mi-152 Fiber Optic Illuminator

See More by [Dolan-Jenner](#)



Mi-152 Fiber Optic Illuminator

Stock **#59-236** ☐ In Stock

-

1

+

€651,00

ADD TO CART

Qty 1+

€651,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Height (inches):
5.5

Length (inches):
8.75

Type: 150 WEKE Quartz Halogen
Voltage (V): 230.00
Weight (lbs): 7.75
Width (inches): 6.00
Intensity Control Option: Yes
Output Power (Lumens): 1750.00
Construction: High Impact Polymer
Lamp Lifetime (hours): 1000 - 10,000
Color Temperature (K): 3200.00
Type of Illumination: Fiber Optic Illuminator, Incandescent
Manufacturer: Dolan-Jenner
Illumination Mode: Constant

Regulatory Compliance

Reach 174: Compliant
RoHS: Compliant
Certificate of Conformance: View
