

TECHSPEC® 25 x 38mm 60R/40T, NIR Plate Beamsplitter



Visible and NIR Plate Beamsplitters

Stock **#68-408** 3-4 DAYS



1



€173,00

ADD TO CART

Qty 1-5

€173,00

Qty 6+

€139,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
45

Clear Aperture (%):
>85

Coating Specification:
Surface 1: 60/40 ±5% @ 900nm, ±10% @ 700 -

1100nm Surface 2: AR $R_{avg} \leq 1\%$, $R_{abs} \leq 2\%$ @ 700 - 1100nm
Construction: Plate
Dimensions (mm): 25.0 x 38.0 +0.0/-0.25
Edges: Cut with 0.25mm maximum edge chip
Note: Beamsplitter-coated side is marked with a black dot
Parallelism (arcmin): ≤ 3
Reflection/Transmission Ratio (R/T): 60/40
Substrate: ☐ N-BK7
Surface Flatness (P-V): 1 λ per inch
Surface Quality: 60-40
Thickness (mm): 3.00 $\pm$ 0.25
Type: Standard Beamsplitter
Wavelength Range (nm): 700 - 1100

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant