

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Gorilla® Glass Windows



Stock #17-161 3-4 DAYS



1



€107,50

ADD TO CART

Qty 1-5

€107,50

Qty 6+

€82,75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):

8
Clear Aperture (%) : 90.00
Clear Aperture CA (mm) : 225.00 x 225.00
Dimensions (mm) : 250.00 x 250.00
Thickness (mm) : 1.10 (nominal)
Coating : Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 7.58 (0 to +300°C)
Density (g/cm³) : 2.39
Edges : Cut and Seamed
Index of Refraction n_d : 1.5
Poisson's Ratio : 0.22
Substrate : Gorilla® Glass
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 350 - 2200
Young's Modulus (GPa) : 70
Length (mm) : 250.00
Width (mm) : 250.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 233 : Compliant