

**TECHSPEC® 25/25.4mm Diameter, T-Mount Thick Optic Mount**



Stock **#52-293** ☐ In Stock

-

1

+

**€63,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-4                       |
| €63,00                        |
| Qty 5+                        |
| €56,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:  
Fixed

Diameter of Compatible Optics (mm):  
25.0 - 25.4

Extension Length (mm):

|                                                           |
|-----------------------------------------------------------|
| 21.5                                                      |
| <b>Construction:</b><br>Black Anodized Aluminum (6061 T6) |
| <b>Total Length (mm):</b><br>24.95                        |
| <b>Type of Optics:</b><br>Circular                        |
| <b>Outer Diameter (mm):</b><br>48.0                       |
| <b>Thread Type:</b><br>T-Mount                            |
| <b>Clear Aperture CA (mm):</b><br>24.0                    |
| <b>Function:</b><br>Optic Mount (Fixed)                   |
| <b>Max. Thickness of Compatible Optics (mm):</b><br>15.50 |
| <b>Min. Thickness of Compatible Optics (mm):</b><br>5.00  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |