

## 254 x 313mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #46-654 3-4 DAYS

⊖ 1 ⊕ **€153,00**

**ADD TO CART**

Qty 1-5

€153,00

Qty 6+

€122,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Surface Flatness (P-V):**  
4 - 6λ

**Substrate:**   
Float Glass

**Surface Quality:**  
80-50

**Dimensions (mm):**  
254.0 x 313.0 ±0.76

**Coating Specification:**  
R<sub>avg</sub> >85% @400 - 700nm

**Coating:**  
Protected Aluminum (400-700nm)

**Coating Type:**  
Metal

**Angle of Incidence (°):**  
45.00

**Bevel:**  
Protective as needed

**Clear Aperture (%):**  
>90

**Thickness (mm):**  
3.00

**Type:**  
Flat Mirror

**Wavelength Range (nm):**  
400 - 700

**Length (mm):**  
313.00

**Width (mm):**  
254.00

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**REACH 241:**  
[Compliant](#)

---