

TECHSPEC® 25.4mm Dia. x 250mm FL, Uncoated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#38-630** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€181,00**

ADD TO CART

Qty 1-5

€181,00

Qty 6+

€144,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.025

Effective Focal Length EFL (mm):
250.00 @ 355nm

Back Focal Length BFL (mm):

247.36
Coating: Uncoated
Substrate: ☐ Fused Silica (Coming 7980)
Surface Quality: 10-5
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ10
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 3.27
Radius R₁ (mm): 119.02
Clear Aperture CA (mm): 21.59
f/#: 9.84
Numerical Aperture NA: 0.05
Type: Plano-Convex Lens
Bevel: Protective Bevel As Needed
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View