

TECHSPEC®

# 25.4mm Dia. x 35mm FL, Uncoated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#39-531** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕

€315,00

ADD TO CART

Qty 1-10

€315,00

Qty 11+

€283,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



**Diameter (mm):**  
25.40 +0.00/-0.10

**Effective Focal Length EFL (mm):**  
35.00 @ 10.6µm

|                                                                                                                                |
|--------------------------------------------------------------------------------------------------------------------------------|
| <b>Back Focal Length BFL (mm):</b><br>33.46                                                                                    |
| <b>Coating:</b><br>Uncoated                                                                                                    |
| <b>Substrate:</b> <br>Coherent® Infrared ZnSe |
| <b>Surface Quality:</b><br>40-20                                                                                               |
| <b>Power (P-V) @ 632.8nm:</b><br>λ                                                                                             |
| <b>Power (P-V) @ 10.6μm:</b><br>λ10                                                                                            |
| <b>Irregularity (P-V) @ 10.6μm:</b><br>λ20                                                                                     |
| <b>Centering, ETD (μm):</b><br>≤12.7                                                                                           |
| <b>Center Thickness CT (mm):</b><br>3.70 ±0.10                                                                                 |
| <b>Edge Thickness ET (mm):</b><br>2.03                                                                                         |
| <b>Radius R<sub>1</sub> (mm):</b><br>49.10                                                                                     |
| <b>Clear Aperture CA (mm):</b><br>22.86                                                                                        |
| <b>f#:</b><br>1.38                                                                                                             |
| <b>Numerical Aperture NA:</b><br>0.36                                                                                          |
| <b>Type:</b><br>Plano-Convex Lens                                                                                              |
| <b>Bevel:</b><br>Protective bevel as needed                                                                                    |
| <b>Wavelength Range (nm):</b><br>600 - 18000                                                                                   |
| <b>Bulk Absorption Coefficient (cm<sup>-1</sup>):</b><br><0.0005 @ 10.6μm                                                      |
| <b>Surface Roughness (Angstroms):</b><br><50 RMS                                                                               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |