

TECHSPEC®

25.4mm Sq., 2X, Protected Gold Off-Axis Ellipsoidal Mirror



Protected Gold Off-Axis Ellipsoidal Mirror

Stock #12-496 3-4 DAYS



1



€335,00

ADD TO CART

Qty 1-5

€335,00

Qty 6+

€301,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Magnification:
2X

Substrate:
Aluminum 6061-T6

Surface Quality:
60-40

Surface Roughness (Angstroms): <100 RMS
Coating: Protected Gold (700-10000nm)
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Dimensions (mm): 25.40 x25.40
Off-Set Angle (°): 72.89
Type: Off-Axis Ellipsoidal Mirror
Wavelength Range (nm): 700 - 10000
Y Offset (mm): 38.10
Image Distance (mm): 50.80
Object Distance (mm): 25.40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View