

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm VIS 0° λ/4 Fresnel Rhomb Retarder



Stock #36-141 3-4 DAYS

1 €315,00

ADD TO CART

Qty 1-5

€315,00

Qty 6+

€289,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
18.81 x 18.81

Coating:
VIS 0° (425-675nm)

Design Wavelength DWL (nm): 532
Substrate: N-BK7
Retardance: λ/4
Surface Quality: 20-10
Type: Fresnel Retarder
Dimensional Tolerance (mm): ±0.10
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Width (mm): 25.40
Entrance and Exit Surface (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
