

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25.4mm Dia., 343nm, $\lambda/2$ High Energy waveplate



High Energy Quartz Waveplates

Stock #39-163 3-4 DAYS



1



€755,00

ADD TO CART

Qty 1-10

€755,00

Qty 11+

€705,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
18.0

Coating:
R_{avg} <0.3%

Design Wavelength DWL (nm):
343

Diameter (mm): 25.40
Substrate: Crystalline Quartz
Retardance: λ/2
Surface Quality: 20-10
Type: High Energy Waveplate
Dimensional Tolerance (mm): +0/-0.2
Construction: Optically Bonded on UVFS (C7980) Substrate
Transmitted Wavefront, P-V: <λ/10 @ 632.8nm
Parallelism (arcsec): <3
Retardance Tolerance: λ/150 @ 20°C
Mount Thickness (mm): 6 ±0.2
Damage Threshold, By Design: >20 J/cm² @ 1064nm, 10ns, 10Hz
Retardance Order: 1st

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant