

25.4mm Dia f/8 Uncoated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#48-174** 3-4 DAYS

- 1 +

€55,00

ADD TO CART

Qty 1-10
€55,00
Qty 11+
€45,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40 ±0.1

Effective Focal Length EFL (mm):
203.00 @632.8nm

Numerical Aperture NA: 0.06
Back Focal Length BFL (mm): 200.1
Substrate: ☐ PMMA
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 632.8
Coating: Uncoated
Clear Aperture CA (mm): 23.9
Edge Thickness ET (mm): 4.00
Center Thickness CT (mm): 4.72
f/#: 8.00
Bevel: Protective bevel as needed
Operating Temperature (°C): 80.00
Radius R (mm): 99.57
Type: Aspheric Lens
Wavelength Range (nm): 400 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View