

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Zinc Selenide (ZnSe) Aspheric Lenses

Stock **#39-477** 3-4 DAYS

[Other Coating Options](#)



1



€980,00

ADD TO CART

Qty 1-10

€980,00

Qty 11+

€888,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
25.40

Numerical Aperture NA: 0.50
Back Focal Length BFL (mm): 23.53
Substrate:  Coherent® Infrared ZnSe
Asphere Figure Error, RMS @ 632.8nm: λ/2
Coating: Uncoated
Centering (arcmin): ≤3
Centering, ETD (μm): ≤12.7
Surface Quality: 40-20
Clear Aperture CA (mm): 22.86
Edge Thickness ET (mm): 2.29
Center Thickness CT (mm): 4.50 ±0.10
f#: 1
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 18000
Conjugate Distance: Infinite
Surface Roughness (Angstroms): <50 RMS
Power (P-V) @ 10.6μm: λ/10
Power (P-V) @ 632.8nm: λ/10

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View