

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock #34-621 3-4 DAYS



1



€100,00

ADD TO CART

Qty 1-5

€100,00

Qty 6+

€80,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

25.40 +0.0/-0.025

Effective Focal Length EFL (mm):

-25.00

Substrate:

[N-BK7](#)

f##: 1	
Numerical Aperture NA: 0.17	
Coating: Uncoated	
Type: Cylinder Lens, Plano-Concave	
Wavelength Range (nm): 350 - 2200	
Back Focal Length BFL (mm): -26.98	
Bevel: Protective bevel as needed	
Center Thickness CT (mm): 3.00	
Center Thickness Tolerance (mm): ±0.1	
Clear Aperture CA (mm): 22.86	
Edge Thickness ET (mm): 12.65	
Radius R ₁ (mm): 12.92	
Surface Quality: 40-20	
Power (P-V) @ 632.8nm: 1.5λ	
Irregularity (P-V) @ 632.8nm: λ/4	
Plano Axis Wedge (arcmin): <5	
Power Axis Wedge (arcmin): <5	

Regulatory Compliance

RoHS: Compliant	
Certificate of Conformance: View	