

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-025 3-4 DAYS



1



€1.590,00

ADD TO CART

Qty 1+

€1.590,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Focal Length FL (mm):
255.00

Model Number:
601948

Maximum Diameter (mm):
119.8 +0/-0.2

Scan Angle (°):
53.2

Scan Field (mm):

169 x 169
Mounting Threads: M85 x 1
Telecentricity (°): F-Theta Only: 14.3 With Scanner: 15
Type: JENar F-Theta
Weight (g): 1400
Working Distance (mm): 291
Note: + VS options provide >85% Transmission from 500-680nm
Wavelength Range (nm): 500 - 680, 1030 - 1080
Protective Window: #17-697 : One Included
Manufacturer: Jenoptik
Scan Field Diameter (mm): 239
Range Distance (mm): 336
Focus Size Diameter, 1/e² (µm): 24
GDD Specification (fs²): 3670
Input Beam Diameter, 1/e² (mm): 20
Maximum Length (mm): 65.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View