

2.5X ZEISS A-Plan Objective

See More by [ZEISS](#)



ZEISS A-Plan Objectives



Stock #13-814 [CONTACT US](#)

1 **€418,00**

ADD TO CART

Qty 1+

€418,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
9.2

Focal Length FL (mm):
65.80

Model Number:
421020-9900-000

Length excluding Threads (mm):
34.50

Magnification:
2.5X

Maximum Diameter (mm):
30

Numerical Aperture NA:
0.06

Mounting Threads:
M27 x 0.75

Compatible Tube Lens Focal Length (mm):
Focal Length: 164.50mm

Type:
Microscope Objective

Typical Applications:
Fluorescence, BrightField

Resolving Power (μm):
4.6

Depth of Field (μm):
76.40

Operating Temperature ($^{\circ}\text{C}$):
+10 to +40

Operating Humidity:
75% at 35 $^{\circ}\text{C}$

Working Distance (mm):
10.4

Weight (g):
120

Wavelength Range (nm):
480 - 650

Style:
Infinity Corrected

Manufacturer:
ZEISS

Field Number (mm):
23

Parfocal Length (mm):
45.06

Immersion Liquid:
N/A

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)