

25° Diffusing Angle 8" x 8" Unmounted Sheet



Stock **#65-888** CLEARANCE 3-4 DAYS

-

1

+

€457,50

ADD TO CART

Qty 1+

€457,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):
±2.5

Diffusing Angle (°):
25 (FWHM)

Dimensional Tolerance (mm):
±0.5

Dimensions (inches):
8 x 8

Dimensions (mm):
203.20 x 203.20

Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 0.78
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Width (mm): 203.20
Construction: Unmounted
Damage Threshold, By Design: ☐ 0.22 J/cm² @ 1064nm, 10ns (typical)
Length (mm): 203.20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant