

25mW, 1064nm DPSS Pointing Laser



DPSS Pointing Lasers

Stock #19-473 3-4 DAYS



1



€515,00

ADD TO CART

Qty 1-9

€515,00

Qty 10+

€464,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
23 to 27

Operating Voltage (V):
3

Output Power (mW):
25

Spatial Mode: TEM ₀₀
Wavelength (nm): 1,064.00 ±2
Wavelength Tolerance (nm): ±2
Power Supply: Power Supply Required and Sold Separately: USA: #19-475 Europe: #19-475 Japan: Not Available Korea: Not Available China: #19-475
Modulation Frequency (kHz): 0-1
Note: Compatible TEC Controller (#19-476) sold separately
Beam Diameter (mm): 1.5 Typical
Beam Divergence (mrad): <1.5 Typical
Laser Class - CDRH: IIIb
Color: Infrared
Length (mm): 90.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant