

25mm Radius, ±10° Tilt, Micro Manual Goniometer



Micro Manual Goniometers

Stock **#13-779** [CONTACT US](#)

- 1 + **€2.476,00**

ADD TO CART

Qty 1+

€2.476,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Goniometer

Type of Drive:
Lead Screw

Type:
English

Stage Size (mm):
66 x 19.1

Travel (°):

±10
Thickness (mm): 17.70
Leadscrew Pitch (mm): 0.32
Load Capacity, Normal (kg): 0.45
Mounting Threads: (10) 0-80
Radius R (mm): 25
Stage Size (inches): 2.6 x 0.75
Weight (g): 40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View