

TECHSPEC® 25mm VIS-EXT, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock #11-289 3-4 DAYS

⊖ 1 ⊕ **€283,00**

ADD TO CART

Qty 1-5
€283,00

Qty 6+
€222,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: VIS-EXT (400-640nm)
Coating Specification: R _{avg} <0.5% @ 400 - 640nm
Construction: Cube
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Reflection/Transmission Ratio (R/T): 50/50
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 400 - 640
 Ts-Tp : <6%
Absolute Transmission (%): 45 ±10

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View