


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Fused Silica Wedge Prisms

Stock #39-072 CLEARANCE 3-4 DAYS



1



€109,95

ADD TO CART

Qty 1+

€109,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Laser V-Coat (266nm)

Angle Tolerance (arcsec):
15

Bevel:
Protective bevel as needed

Coating Specification:
R_{abs} <0.25% @266nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52
Design Wavelength DWL (nm): 266
Diameter (mm): 25.00
Image Orientation: Beam Deviation
Power (diopters): 8.75
Ray Deviation @ 355nm (°): 5.00
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Thickness (mm): 3.00
Wedge Angle: 10° 17'38"
Note: Specificy this is S1 & S2 power and irregularity, not the overall power of the wedge
Damage Threshold, By Design: ☐ 3 J/cm² @ 266nm, 20ns, 20Hz
Power (fringes) @ 632.8nm: 0.50
Irregularity (fringes) @ 632.8nm: 0.20

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View