

**TECHSPEC® 25mm Dia x 50mm FL Uncoated, Illumination Grade PCX Cylinder Lens**



Stock **#46-016** 3-4 DAYS

⊖ 1 ⊕ **€70,00**

ADD TO CART

|         |
|---------|
| Qty 1-5 |
| €70,00  |

|        |
|--------|
| Qty 6+ |
| €56,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
25.00

Effective Focal Length EFL (mm):  
50.00

Substrate: ☐  
**N-BK7**

|                                                 |
|-------------------------------------------------|
| <b>f/#:</b><br>2                                |
| <b>Numerical Aperture NA:</b><br>0.25           |
| <b>Coating:</b><br>Uncoated                     |
| <b>Type:</b><br>Cylinder Lens, Plano-Convex     |
| <b>Wavelength Range (nm):</b><br>350 - 2200     |
| <b>Back Focal Length BFL (mm):</b><br>47.20     |
| <b>Center Thickness CT (mm):</b><br>4.24        |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1 |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2 |
| <b>Edge Thickness ET (mm):</b><br>1.03          |
| <b>Focal Length Tolerance (%):</b><br>±3        |
| <b>Radius R<sub>1</sub> (mm):</b><br>25.93      |
| <b>Surface Quality:</b><br>60-40                |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---