

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25mm Dia X -12.5mm FL, Protected Gold, Convex Mirror



Convex Mirrors

Stock #87-688 3-4 DAYS



1



€62,00

ADD TO CART

Qty 1-5

€62,00

Qty 6+

€49,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Focal Length FL (mm):
-12.50

Center Thickness CT (mm):
5.00

Clear Aperture (%): 90.00
Coating: Protected Gold (700-10000nm)
Coating Specification: R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 1.65
Focal Length Tolerance (%): ±2
Radius R (mm): 25.0
Substrate: ☐ N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 700 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
